



VT09F

## 9M 1Row DIN Flush Metal BOX, No Door

### Technical properties

#### Connection

|                          |    |
|--------------------------|----|
| Number of conduit inlets | 16 |
|--------------------------|----|

#### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 230 - 415 V |
|-----------------|-------------|

#### Installation, mounting

|                            |    |
|----------------------------|----|
| Suitable for outdoor usage | No |
|----------------------------|----|

#### Equipment

|                 |   |
|-----------------|---|
| Number of rails | 1 |
|-----------------|---|

|                |   |
|----------------|---|
| Number of rows | 1 |
|----------------|---|

#### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 9 |
|-------------------|---|

#### Dimensions

|        |        |
|--------|--------|
| Height | 295 mm |
|--------|--------|

|       |        |
|-------|--------|
| Width | 304 mm |
|-------|--------|

|       |       |
|-------|-------|
| Depth | 10 mm |
|-------|-------|

|                |       |
|----------------|-------|
| Built-in depth | 60 mm |
|----------------|-------|

|                       |   |
|-----------------------|---|
| Number of width units | 9 |
|-----------------------|---|

#### Cover, door

|                 |   |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

#### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

#### Materials

|          |       |
|----------|-------|
| Material | Steel |
|----------|-------|

|          |      |
|----------|------|
| RAL code | 9002 |
|----------|------|

|        |            |
|--------|------------|
| Colour | Grey white |
|--------|------------|

#### Safety

|                  |                   |
|------------------|-------------------|
| Protection class | Isolation class I |
|------------------|-------------------|

|                      |      |
|----------------------|------|
| Impact resistance IK | IK05 |
|----------------------|------|