



VS112PT



Small distributor,golf,surface,1row,IP40,12M,MS-terminal,N+PE,white door

Technical properties

Functions

| | |
|---------------------|-----|
| With a pipe-in lead | Yes |
|---------------------|-----|

Configuration

| | |
|-------------------|---------------|
| Module | consumer unit |
| Number of modules | 12 |

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 400 V |
|-----------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 80 A |
|---------------|------|

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 99 mm |
| Internal depth | 99 mm |
| Height of installed product | 252 mm |
| Width of installed product | 282 mm |
| Width in division units | 12 |

Cover, door

| | |
|------------------------------------|----------------|
| Identification of protection index | 40 |
| Interlockable | No |
| Number of keylock of the door | 0 |
| Cover type | Closed (plain) |
| Door locking | without |
| Door leave | single |
| Cover type | Door |
| Transparent cover or door | No |

Materials

| | |
|---------------------------|-----------------------|
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | plastic |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

Settings

| | |
|----------------|---------------------------|
| Enclosure type | Distributor empty cabinet |
|----------------|---------------------------|

Equipment

| | |
|--------------------------------------|-----|
| Number of rows | 1 |
| Quantity of section in width | 1 |
| Quantity of rails | 1 |
| Can be accessorized | Yes |
| Number of openings for flange plates | 0 |
| Extension possible | Yes |
| Earthing terminal block | Yes |
| Neutral terminal block | Yes |
| Signal passing door | Yes |

Standards

| | |
|--------------------|--------|
| GWT Glow wire test | 650 °C |
|--------------------|--------|

Safety

| | |
|---|---------------|
| IK protection code against mechanical impacts | IK07 |
| Protection class | isol.class II |
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |
| Impact strength | IK07 |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -25...40 °C |
|-----------------------|-------------|