



WBHSV5-MW



Allure 5 Gang Switch Plate cw mechs MW

Technical properties

Architecture

Type of control unit rocker

Configuration

Switch mode 2 way, with loop terminal

Controls and indicators

Number of buttons 5

Main electrical features

Nominal voltage 250 V AC

Frequency 50 Hz

Electric current

Rated current 16 AX

Dimensions

Height 117 mm

Width 77 mm

Installation, mounting

Entries cable entries bevelled

Mounting type flush-mounted

Installation mode for screw fastening

Connection

Terminal terminals accommodate 4 x 1.5 mm² cable

Type of connection with screw terminals

Type of connection Screw connection

Scope of delivery

Scope of delivery supplied with standard tapered point 32 mm fixing screws

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Identification

Main design line Allure