



WBM10I

Mechanism 10A intermediate

Technical properties

Architecture

| | |
|----------------------|--------|
| Type of control unit | rocker |
|----------------------|--------|

Configuration

| | |
|-------------------------|--------------|
| Switch mode | intermediate |
| Antibacterial treatment | No |

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V AC |
|-----------------|----------|

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Materials

| | |
|--------|-------|
| Colour | white |
|--------|-------|

Connection

| | |
|--------------------|----------------------|
| Type of connection | with screw terminals |
| Type of connection | Screw connection |

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |