



WBMDUPB

Mechanism push dimmer trailing-edge

Technical properties

Architecture

Type of control unit Push button

Main electrical features

Nominal voltage 230 V

Frequency 50 Hz

Voltage

Operating voltage 230 V~ +10%/-15%

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Dimensions

Depth 51 mm

Height 24 mm

Width 24 mm

Power

Power consumption (standby) max. 0.1 W

Electronic transformers 20...350 W

Measurement

Extension unit input with extension unit input for slave push-button
WBMSLL

Materials

Colour white

Material Polycarbonate (PC)

LED control

Dimmable 230 V LED lamps 2.5...250 W

LED with blue status LED

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 7...300 W

Installation, mounting

Installation mode RotoLoc ®

Connection

Conductor cross-section 1.5 mm²

Cable

Cable length, extensions	max. 20 m
--------------------------	-----------

Equipment

On/Off switch	Yes
---------------	-----

Dimming principle	phase cut-off
-------------------	---------------

Brightness	with brightness memory
------------	------------------------

Safety

Halogen free	Yes
--------------	-----

Use conditions

Operating temperature	-5...50 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

Temperature	with overheating protection
-------------	-----------------------------

Identification

Main design line	Mechanisms
------------------	------------