



181113

Push-button, NO contact, TS, stainless steel matt, brushed nickel

Technical properties

Architecture

Type of control unit	Push button
----------------------	-------------

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	12 V
-----------------	------

Rated voltage	12 V
---------------	------

Electric current

Momentary-contact current	1.5 A
---------------------------	-------

Dimensions

Depth	19.7 mm
-------	---------

Insertion depth	13 mm
-----------------	-------

Height	22 mm
--------	-------

Width	22 mm
-------	-------

Materials

Colour of design line	stainless steel
-----------------------	-----------------

Colour	stainless steel
--------	-----------------

Material / workmanship	Nickel brushed
------------------------	----------------

Surface appearance	matt
--------------------	------

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Scope of delivery

With lamp	No
-----------	----

Equipment

Quantity of NC contacts	1
-------------------------	---

Quantity of NO contacts	1
-------------------------	---

Safety

Protection index IP	IP20
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
Use conditions	
Operating temperature	-20...60 °C
Identification	
Main design line	Berker TS
Instructions	
Special note text	For connection via system interfaces to radio bus, KNX radio or KNX installations. Alternatively, can be used to control relay circuits.