



WBMDUR



Mechanism rotary dimmer trailing-edge

Technical properties

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
Material	Polycarbonate (PC)

Dimensions

Height	24 mm
Width	24 mm
Depth	65 mm

Architecture

Control/operation element	Push & rotary switch
---------------------------	----------------------

Power

Power consumption standby	0,10 W
---------------------------	--------

Lighting

Dimmable 230 V LED lamp	3 - 250 W
-------------------------	-----------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Capacity

Number of modules	1
-------------------	---

Texts

Dimming principle	Phase cut-off
Extension unit input	With extension unit input for slave push-button WBMESL
Fuse	Short-circuit and overload-proof (electronic fuse)
Installation mode	RotoLoc®
Operation and control	No Bluetooth interface
Type of connection	With screw terminals