



WBMDUR

## Mechanism rotary dimmer trailing-edge

### Technical properties

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Materials

Colour	White
Material	Polycarbonate (PC)

#### Dimensions

Height	24 mm
Width	24 mm
Depth	65 mm

#### Architecture

Control/operation element	Push & rotary switch
---------------------------	----------------------

#### Power

Power consumption standby	0,10 W
---------------------------	--------

#### Lighting

Dimmable 230 V LED lamp	3 - 70 W
-------------------------	----------

#### Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

#### Capacity

Number of modules	1
-------------------	---

#### Texts

Dimming principle	Phase cut-off
Extension unit input	With extension unit input for slave push-button WBMESL
Fuse	Short-circuit and overload-proof (electronic fuse)
Installation mode	RotoLoc®
Operation and control	No Bluetooth interface
Type of connection	With screw terminals