



20267103

Thermostat, change-over contact, centre plate, K.5, al., matt, lacq.

Technical properties

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

Electric current

Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A
"Switching current ""Cooling"" at $\cos \varphi = 0.6$ "	2 A
"Switching current ""Cooling"""	5 A

Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

Materials

Colour	aluminium
Material / workmanship	lacquered
Material	Plastic/metal

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with plug-in terminals
--------------------	------------------------

Equipment

Switching temperature difference	≈ 0.5 K
Heating	for heating or cooling mode
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

temperatur

Temperature	5...30 °C
-------------	-----------

Identification

Application, usage	HVAC control
Main design line	Berker K.5