



20302045

**Thermostat, NC contact, centre plate, rocker switch, R.1/R.3, black glossy**

**Technical properties**

**Functions**

Switching with on/off switch and indicator LED for "on"

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50 Hz

**Voltage**

Rated surge voltage	4 kV
---------------------	------

**Electric current**

Inductive load at $\cos \varphi = 0.6$	max. 4 A
Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A
Switching current	10 A

**Measurement**

Range of temperatures	5 / 30 °C
-----------------------	-----------

**Materials**

Colour of design line	black
Colour	black
Material	Plastic/metal

**Installation, mounting**

Installation mode	without spreader claws
-------------------	------------------------

**Connection**

Type of connection	with screw terminals
Connection	with separate connection for night lowering

**Equipment**

Night lowering	≈ 4 K
Switching temperature difference	≈ 0.5 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

**Use**

Differentiation characteristic 1 - Sales	with rocker switch
--	--------------------

**Safety**

---

Degree of contamination	2
-------------------------	---

**Use conditions**

---

Energy efficiency class	I (1%)
-------------------------	--------

**temperatur**

---

Temperature	5...30 °C
-------------	-----------

**Identification**

---

Application, usage	HVAC control
--------------------	--------------

---

Main design line	Berker R.1/R.3/R.8
------------------	--------------------

---

Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8
--------------------------	------------------------------------

**Instructions**

---

Special note text

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!