



WBMDUR

## Mechanism rotary dimmer trailing-edge

### Technical properties

#### Architecture

Type of control unit	Push & rotative
----------------------	-----------------

#### Main electrical features

Frequency	50 Hz
-----------	-------

#### Fuse

Fuse	short-circuit and overload proof (electronic fuse)
------	--

#### Dimensions

Depth	65 mm
Height	24 mm
Width	24 mm

#### Power

Power consumption (standby)	max. 0.1 W
Electronic transformers	20...350 W

#### LED control

Dimmable 230 V LED lamps	2.5...250 W
--------------------------	-------------

#### Incandescent bulbs control

230 V incandescent lamps and halogen lamps	7...300 W
--	-----------

#### Connection

Conductor cross-section	1.5 mm <sup>2</sup>
-------------------------	---------------------

#### Equipment

On/Off switch	Yes
Dimming principle	phase cut-off
Brightness	with brightness memory

#### Use conditions

Operating temperature	-5...50 °C
Storage/transport temperature	-20...70 °C
Temperature	with overheating protection