



20316084

therm. 24 V w. NC cont., Centre pl., rocker sw. a. LED, Q.x, alu velvety lacq.

#### Technical properties

#### Functions

Switching with on/off switch and indicator LED for "on"

#### Main electrical features

Nominal voltage	24 V
Rated voltage	24 V AC/DC
Frequency	50/60 Hz

#### Electric current

Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A

#### Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

#### Materials

Colour of design line	aluminium
Material / workmanship	lacquered

#### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

#### Connection

Type of connection	with plug-in terminals
Connection	with separate connection for night lowering

#### Equipment

Night lowering	≈ 4 K
Switching temperature difference	≈ 0.5 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

#### Use

Differentiation characteristic 1 - Sales	with rocker switch
--	--------------------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

#### Use conditions

**temperatur**

Temperature

5...30 °C

**Identification**

Application, usage

HVAC control

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9