



WBMDUR

## Mechanism rotary dimmer trailing-edge

### Technical properties

#### Architecture

Type of control unit Push & rotative

#### Main electrical features

Frequency 50 Hz

#### Voltage

Operating voltage 230 V~ +10%/-15%

#### Fuse

Fuse short-circuit and overload proof (electronic fuse)

#### Dimensions

Depth 65 mm

Height 24 mm

Width 24 mm

#### Power

Power consumption (standby) max. 0.1 W

Electronic transformers 20...350 W

#### Measurement

Extension unit input with extension unit input for slave push-button WBMSLL

#### LED control

Dimmable 230 V LED lamps 2.5...250 W

#### Incandescent bulbs control

230 V incandescent lamps and halogen lamps 7...300 W

#### Installation, mounting

Installation mode RotoLoc ®

#### Connection

Conductor cross-section 1.5 mm<sup>2</sup>

#### Cable

Cable length, extensions max. 20 m

#### Equipment

On/Off switch Yes

---

Dimming principle	phase cut-off
-------------------	---------------

Brightness	with brightness memory
------------	------------------------

---

**Safety**

Halogen free	Yes
--------------	-----

---

**Use conditions**

Operating temperature	-5...50 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

Temperature	with overheating protection
-------------	-----------------------------

---

**Identification**

Main design line	Mechanisms
------------------	------------