




WBME5A



Mechanism, 5A electronic push button

Technical properties

Main electrical features

Frequency 50 Hz

Power

Dimmable conventional transformers max. 500 VA

Power consumption (standby) ≤ 0.35 W

Electronic transformers max. 500 W

Measurement

Extension unit input with extension unit input for slave push-button WBMESL

Fluorescent bulbs control

Compact fluorescent lamps max. 500 VA

LED control

LED with configurable status LED (orange/blue)

Incandescent bulbs control

230 V incandescent lamps and halogen lamps max. 1200 W

Installation, mounting

Installation mode RotoLoc ®

Connection

Screw terminals (max.) 2 x 1,5/1 x 2,5 mm²

Type of connection with screw terminals

Cable

Cable length, extensions max. 40 m

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature 5...40 °C

Storage/transport temperature -20...60 °C

Identification

Main design line silhouette