



20302089

Thermostat, NC contact, centre plate, rocker switch, R.1/R.3, p. white glossy

Technical properties

Functions

Switching with on/off switch and indicator LED for "on"

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50 Hz

Voltage

Rated surge voltage	4 kV
---------------------	------

Electric current

Inductive load at $\cos \varphi = 0.6$	max. 4 A
Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A
Switching current	10 A

Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

Materials

Colour of design line	polar white
-----------------------	-------------

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with screw terminals
Connection	with separate connection for night lowering

Equipment

Night lowering	≈ 4 K
Switching temperature difference	≈ 0.5 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

Use

Differentiation characteristic 1 - Sales	with rocker switch
--	--------------------

Safety

Degree of contamination	2
-------------------------	---

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

temperatur

Temperature	5...30 °C
-------------	-----------

Identification

Application, usage	HVAC control
--------------------	--------------

Main design line	Berker R.1/R.3/R.8
------------------	--------------------

Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8
--------------------------	--------------------------------------

Instructions

Special note text

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!