



28342089

Rot. dimmer centre plate (R, L, C), soft-lock, R.classic, p. white glossy

Technical properties

Architecture

Type of control unit	Push & rotative
----------------------	-----------------

Functions

Soft startup	bulb-preserving soft startup
--------------	------------------------------

Main electrical features

Nominal voltage	230 V
Frequency	50/60 Hz

Voltage

Operating voltage	230 V AC
Voltage	voltage test possible without dismantling

Fuse

Fuse	short-circuit and overload proof (electronic fuse)
------	--

Dimensions

Axis dimension Ø	4 mm
------------------	------

Power

Dimmable conventional transformers	50...420 VA
connected load	50...420 W/VA
Loss power at full load	≈ 5 W
Electronic transformers	50...420 W

Measurement

Extension unit input	with input for extension units insert for universal rotary dimmer
----------------------	---

Materials

Colour of design line	polar white
Colour	polarwhite

Incandescent bulbs control

230 V incandescent lamps and halogen lamps	50...420 W
--	------------

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of load	universal
--------------	-----------

Scope of delivery

Component	with incremental encoder
-----------	--------------------------

Equipment

Dimming principle	phase cut-on or cut-off according to load type, self-learning
low noise	very low noise
Brightness	with brightness memory

Use

Differentiation characteristic 3 - Sales	Soft-lock
--	-----------

Use conditions

Operating temperature	5...25 °C
-----------------------	-----------

Identification

Main design line	Serie R.classic
------------------	-----------------

Instructions

Information text	Trouble-free operation will be obtained only with Berker TronicÂ® transformers.
------------------	---