



29516084

## LED signal light RGB Q.1/Q.3 alu velvety, lacquered

### Technical properties

#### Architecture

Fixing mode flush-mounting

#### Main electrical features

Rated voltage 230 V AC

Frequency 50/60 Hz

#### Power

Power consumption at 195 ... 265 V~, 50/60 Hz - max. 2 W

#### Materials

Colour aluminium

Colour aluminium optics

RAL colour RAL 9006 - White aluminium

Material / workmanship lacquered

Material Plastic/metal

Surface appearance velvety

#### LED control

Quantity LED lamps 4

#### Installation, mounting

For installation in standard wall boxes according to DIN 49073-1

#### Connection

Conductor cross-section 2.5 mm<sup>2</sup>

#### Settings

Setting Brightness modifiable via potentiometer

#### Equipment

Lighting Colour sequence can be stopped at any position via the push-button., Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button

Switches / socket outlets colour is switchable via an external switch

#### Use cases

Application Light control

#### temperatur

Ambient temperature -5...40 °C

**Identification**

---

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

**Instructions**

---

Special note text

For consistent illumination of all pilot lamps, connect  
max. 5 devices per 10 m of cable length.