



303212

On/off switch 2pole 16 AX, light control

Technical properties

Architecture

Type of control unit	single rocker
Fixing mode	surface-mounting

Configuration

Switch mode	2-pole off, with predefined neutral position
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

Electric current

Switching current	16 AX (200 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	42 mm
Insertion depth	32 mm
Height	71 mm
Width	71 mm

Materials

Material	Plastic/metal
Surface appearance	matt

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

Heating switch	No
----------------	----

Use cases

Application	Light control
-------------	---------------

Safety

Protection index IP	IP20
---------------------	------

Impact strength	IK07
-----------------	------

Identification

Appliance switch type	No
-----------------------	----

Main design line	Light control
------------------	---------------

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting ; Only suitable in combination with rockers with "0" imprint.
------------------	--
