



20306086

Thermostat, NC contact, centre plate, rocker switch, Q.1/Q.3, ant. velvety lacq.

Technical properties

Functions

Switching	with on/off switch and indicator LED for "on"
-----------	---

With cooling function	Yes
-----------------------	-----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

Electric current

Inductive load at $\cos \varphi = 0.6$	max. 4 A
Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A
Switching current	10 A

Dimensions

Insertion depth	24.5 mm
-----------------	---------

Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

Materials

Colour of design line	anthracite
Colour	anthracite
Material / workmanship	lacquered
Material	Plastic/metal

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with plug-in terminals
--------------------	------------------------

Connection	with separate connection for night lowering
------------	---

Equipment

Night lowering	≈ 4 K
----------------	-------

Switching temperature difference	≈ 0.5 K
----------------------------------	---------

Control	setting knob with temperature range limitation
---------	--

Valve drives	e.g. for valve drives closed in de-energised state
--------------	--

Use

Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

temperatur

Temperature	5...30 °C
-------------	-----------

Identification

Application, usage	HVAC control
--------------------	--------------

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------

Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9
--------------------------	--