



20316086

Temp. cont., NC contact, Cen. plate, 24V AC/DC, rocker switch, Q.1/Q.3, ant. velv. lacq.

Technical properties

Functions

Switching with on/off switch and indicator LED for "on"

Main electrical features

Nominal voltage	24 V
Rated voltage	24 V AC/DC
Frequency	50/60 Hz

Electric current

Switching current	10 A~/4 A=
Switching current "Heating" at $\cos \varphi = 0.6$	4 A
Heating switching current	10 A

Measurement

Range of temperatures	5 / 30 °C
-----------------------	-----------

Materials

Colour of design line	anthracite
Colour	anthracite
Material / workmanship	lacquered
Material	Plastic/metal

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with plug-in terminals
Connection	with separate connection for night lowering

Equipment

Night lowering	≈ 4 K
Switching temperature difference	≈ 0.5 K
Control	setting knob with temperature range limitation
Valve drives	e.g. for valve drives closed in de-energised state

Use

Differentiation characteristic 1 - Sales	with rocker switch
--	--------------------

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions	
Energy efficiency class	I (1%)
temperatur	
Temperature	5...30 °C
Identification	
Application, usage	HVAC control
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9