



3036

## Change-over switch 10AX 250V~, Light control

### Technical properties

#### Architecture

Type of control unit	single rocker
Fixing mode	flush-mounting

#### Functions

Switching angle	3.5 °
-----------------	-------

#### Configuration

Switch mode	Off/change-over
Antibacterial treatment	No

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Controls and indicators

Push-buttons	No
--------------	----

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

#### Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

#### Dimensions

Depth	41.6 mm
Insertion depth	31 mm
Height	71 mm
Width	71 mm

#### Materials

Material	Plastic/metal
Surface appearance	matt

#### Installation, mounting

Installation mode	with spreader claws, for screw fastening
-------------------	--

#### Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1

Type of connection	with plug-in terminals
Type of connection	Quickconnect
<b>Equipment</b>	
Lighting	for lighting and monitoring circuit
Heating switch	No
<b>Use cases</b>	
Application	Barrier-free application, HVAC-control, Light control
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07
<b>Identification</b>	
Application, usage	HVAC control, Light control
Appliance switch type	No
Main design line	Light control
<b>Instructions</b>	
Special note text	A control change-over switch is shown here as an example. With 2-pole and 3-pole control on/off switches, other rocker switches and neon lamp units are required.
Information text	spreader claws, insulated to the supporting ring, self-resetting