



3037

## Intermediate switch, light control

### Technical properties

#### Architecture

Type of control unit single rocker

#### Functions

Switching angle 3.5 °

#### Configuration

Switch mode intermediate

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Controls and indicators

Push-buttons No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

#### Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

#### Dimensions

Depth 42 mm

Insertion depth 32 mm

Height 71 mm

Width 71 mm

#### Materials

Surface appearance matt

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

**Equipment**

---

Lighting	for lighting and monitoring circuit
Heating switch	No

---

**Use cases**

---

Application	Barrier-free application ; HVAC-control ; Light control
-------------	---

---

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

---

**Identification**

---

Application, usage	HVAC control ; Light control
Appliance switch type	No
Main design line	Light control

---

**Instructions**

---

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--

---