



20447103

Thermostat, NO contact, centre plate, time-controlled, K.5, al., matt, lacq.

### Technical properties

#### Functions

Function	with frost protection function ; with valve protection function ; timer for changing the temperature by the hour ; with access protection ; Operating hours meter or energy consumption display adjustable
Slide switch	with switchover manual/automatic mode

#### Controls and indicators

Operation	operating languages are adjustable: German, English, Dutch or French
Indication / display	large, backlight display with text display

#### Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50 Hz

#### Electric current

Switching current	10 mA ... 10 (4) A
Switching current at $\cos \varphi = 0.6$	max. 4 A

#### Dimensions

Insertion depth	25 mm
-----------------	-------

#### Power

Power consumption	≈ 1.2 W
-------------------	---------

#### Battery

Lithium cell power reserve [years]	≈ 10
------------------------------------	------

#### Detection

Sensor	with integrated temperature sensor
--------	------------------------------------

#### Materials

Colour of design line	aluminium
Material / workmanship	lacquered

#### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

#### Connection

Type of connection	with screw terminals
Connection	with additional connection for external floor temperature sensor/remote sensor

## Settings

Floor temperature setting range	10...40 °C
Room temperature setting range	5...30 °C
Programs	holiday programme with date activation
Programming	3 blocks of days: Mon-Fri, Sat-Sun, Mon-Sun ; max. 9 switching times per weekday ; programmable with operating unit removed ; 3 preset time programmes, individually adjustable
Time	with automatic summer-/winter time switching (can be switched off)

## Equipment

Switching temperature difference	≈ 0.5 K
Heating	with self-teaching heating curve ; for underfloor heating control using room and/or floor temperature possible ; for room and floor heaters ; for heating or cooling mode
Control	control process PWM or 2-point (on/off) can be selected ; PWM cycle time and hysteresis (for two-point control) settable
Valve drives	type of actuator (currentless closed/open) adjustable

## Use

Differentiation characteristic 2 - Sales	Time-controlled
--	-----------------

## Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

## Use conditions

Temperature	temperature control range adjustable
Energy efficiency class	IV (2%)

## Identification

Application, usage	HVAC control
Main design line	Berker K.5