



3315412045

VGA soc. out., screw-in lift terminals, R.1/R.3, black glossy

Technical properties

Connectivity

| | |
|--------------------|---|
| Outlet | with straight outlet |
| Plug type | S-VGA compatible |
| Connectors / jacks | with 15pole D-subminiature jack (front) |

Frequency

| | |
|-----------------------|--------------|
| Frequency range video | max. 160 MHz |
|-----------------------|--------------|

Screen

| | |
|------------|---------------------|
| Resolution | max. 1280 x 1024 px |
|------------|---------------------|

Materials

| | |
|-----------------------|--------------|
| Colour of labelling | 217,217,217 |
| Colour of design line | black |
| Material for printing | PC-PMA black |
| Surface appearance | glossy |

Installation, mounting

| | |
|-------------------|--|
| Installation mode | without spreader claws ; for screw fastening |
|-------------------|--|

Connection

| | |
|-------------------------|--|
| Conductor cross-section | max. 1.5 mm ² |
| Type of connection | with screw-in lift terminals for connection to 15-core VGA cable |

Settings

| | |
|-------------------|------------|
| Shading parameter | R1_czarny |
| Laser parameter | R1_schwarz |

Equipment

| | |
|------------------------------------|----------------------|
| Type of configuration | Laserdruck |
| Supporting plate / Supporting ring | with supporting ring |

Use

| | |
|--|------------------------------|
| Differentiation characteristic 3 - Sales | with screw-in lift terminals |
|--|------------------------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |

Identification

| | |
|--------------------|--------------------------|
| Application, usage | Communication technology |
|--------------------|--------------------------|

Instructions

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74