



3315412089

**VGA soc. out., screw-in lift terminals, R.1/R.3, p. white glossy**

## Technical properties

### Connectivity

Outlet	with straight outlet
Plug type	S-VGA compatible
Connectors / jacks	with 15pole D-subminiature jack (front)

### Frequency

Frequency range video	max. 160 MHz
-----------------------	--------------

### Screen

Resolution	max. 1280 x 1024 px
------------	---------------------

### Materials

Colour of design line	polar white
Colour	polarwhite
RAL colour	RAL 9010 - Pure white
Material	Plastic/metal
Material for printing	ASA polar white

### Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

### Connection

Conductor cross-section	max. 1.5 mm <sup>2</sup>
Type of connection	with screw-in lift terminals for connection to 15-core VGA cable

### Settings

Shading parameter	R1_biały
Laser parameter	R1_weiß

### Equipment

Type of configuration	Laserdruck
Supporting plate / Supporting ring	with supporting ring

### Use

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

### Safety

REACH conform	Yes
RoHS conform	Yes

### Identification

Subject to technical modifications

Application, usage	Communication technology
Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8

#### Instructions

Information text	<p>For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74</p>
------------------	---