



20447109

Thermostat, NO contact, centre plate, time-controlled, K.1, p. white glossy

Technical properties

Functions

Function	Operating hours meter or energy consumption display adjustable ; timer for changing the temperature by the hour ; with valve protection function ; with access protection ; with frost protection function
Slide switch	with switchover manual/automatic mode
With cooling function	Yes

Controls and indicators

Operation	operating languages are adjustable: German, English, Dutch or French
Indication / display	large, backlight display with text display

Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50 Hz

Electric current

Switching current	10 mA ... 10 (4) A
Switching current at $\cos \varphi = 0.6$	max. 4 A

Dimensions

Insertion depth	25 mm
-----------------	-------

Power

Power consumption	≈ 1.2 W
-------------------	---------

Battery

Lithium cell power reserve [years]	≈ 10
------------------------------------	------

Detection

Sensor	with integrated temperature sensor
--------	------------------------------------

Materials

Colour of design line	polar white
-----------------------	-------------

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with screw terminals
Connection	with additional connection for external floor temperature sensor/remote sensor

Settings

Floor temperature setting range	10...40 °C
Room temperature setting range	5...30 °C
Programs	holiday programme with date activation
Programming	3 preset time programmes, individually adjustable ; programmable with operating unit removed ; 3 blocks of days: Mon-Fri, Sat-Sun, Mon-Sun ; max. 9 switching times per weekday
Time	with automatic summer-/winter time switching (can be switched off)

Equipment

Switching temperature difference	≈ 0.5 K
Heating	for room and floor heaters ; with self-teaching heating curve ; for underfloor heating control using room and/or floor temperature possible ; for heating or cooling mode
Control	control process PWM or 2-point (on/off) can be selected ; PWM cycle time and hysteresis (for two-point control) settable
Valve drives	type of actuator (currentless closed/open) adjustable

Use

Differentiation characteristic 2 - Sales	Time-controlled
--	-----------------

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Temperature	temperature control range adjustable
Energy efficiency class	IV (2%)

Identification

Application, usage	HVAC control
Main design line	Berker K.1