



283410

Rot. dimmer centre plate (R, L, C), soft-lock, 1930/glass, p. white glossy

Technical properties

Architecture

Type of control unit Push & rotative

Functions

Soft startup bulb-preserving soft startup

Main electrical features

Nominal voltage 230 V

Voltage

Operating voltage 230 V AC

Voltage voltage test possible without dismantling

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Dimensions

Axis dimension Ø 4 mm

Power

Dimmable conventional transformers 50...420 VA

connected load 50...420 W/VA

Loss power at full load ≈ 5 W

Electronic transformers 50...420 W

Measurement

Extension unit input with input for extension units insert for universal rotary dimmer

Materials

Colour of design line polar white

Colour polarwhite

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 50...420 W

Installation, mounting

Installation mode for screw fastening

Connection

Type of load universal

Scope of delivery

Component	with incremental encoder
-----------	--------------------------

Equipment

Dimming principle	phase cut-on or cut-off according to load type, self-learning
low noise	very low noise
Brightness	with brightness memory

Use

Differentiation characteristic 3 - Sales	Soft-lock
--	-----------

Use conditions

Operating temperature	5...25 °C
-----------------------	-----------

Identification

Release issue	2
Secondary design line(s)	Serie 1930 ; Serie 1930 Porzellan Made by Rosenthal ; Serie Glass ; Series R.classic

Instructions

Information text	Trouble-free operation will be obtained only with Berker TronicÂ® transformers.
------------------	---