



28342045

## Rot. dimmer centre plate (R, L, C), soft-lock, R.classic, black glossy

### Technical properties

#### Architecture

Type of control unit	Push & rotative
----------------------	-----------------

#### Functions

Soft startup	bulb-preserving soft startup
--------------	------------------------------

#### Main electrical features

Nominal voltage	230 V
Frequency	50/60 Hz

#### Voltage

Operating voltage	230 V AC
Voltage	voltage test possible without dismantling

#### Fuse

Fuse	short-circuit and overload proof (electronic fuse)
------	--

#### Dimensions

Axis dimension Ø	4 mm
------------------	------

#### Power

Dimmable conventional transformers	50...420 VA
connected load	50...420 W/VA
Loss power at full load	≈ 5 W
Electronic transformers	50...420 W

#### Measurement

Extension unit input	with input for extension units insert for universal rotary dimmer
----------------------	---

#### Materials

Colour of design line	black
Colour	black
Material	Plastic/metal

#### Incandescent bulbs control

230 V incandescent lamps and halogen lamps	50...420 W
--	------------

#### Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

#### Connection

Subject to technical modifications

Type of load	universal
Type of connection	with plug-in terminals
<b>Scope of delivery</b>	
Component	with incremental encoder
<b>Equipment</b>	
Dimming principle	phase cut-on or cut-off according to load type, self-learning
low noise	very low noise
Brightness	with brightness memory
<b>Use</b>	
Differentiation characteristic 3 - Sales	Soft-lock
<b>Use conditions</b>	
Operating temperature	5...25 °C
<b>Identification</b>	
Main design line	Serie R.classic
<b>Instructions</b>	
Information text	Trouble-free operation will be obtained only with Berker TronicÂ® transformers.