



303212

On/off switch 2pole 16 AX, light control

Technical properties

Architecture

Type of control unit single rocker

Configuration

Switch mode 2-pole off ; with predefined neutral position

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Electric current

Switching current 16 AX (200 W Self Ballasted Lamp (SBL))

Dimensions

Depth 42 mm

Insertion depth 32 mm

Height 71 mm

Width 71 mm

Materials

Surface appearance matt

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting for lighting and monitoring circuit

Heating switch	No
----------------	----

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Impact strength	IK07
-----------------	------

Identification

Appliance switch type	No
-----------------------	----

Main design line	Light control
------------------	---------------

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting ; Only suitable in combination with rockers with "0" imprint.
------------------	--