



303808

Double change-over switch, isolated input terminals, light control

Technical properties

Architecture

| | |
|----------------------|----------------|
| Type of control unit | double rocker |
| Fixing mode | flush-mounting |

Configuration

| | |
|-------------------------|----|
| Antibacterial treatment | No |
|-------------------------|----|

Compatibility

| | |
|-------------------------|----|
| IFTTT support available | No |
|-------------------------|----|

Controls and indicators

| | |
|--------------|----|
| Push-buttons | No |
|--------------|----|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |
| Frequency | 50/60 Hz |

Electric current

| | |
|-------------------|---|
| Switching current | 10 AX (100 W Self Ballasted Lamp (SBL)) |
|-------------------|---|

Dimensions

| | |
|-----------------|---------|
| Depth | 41.6 mm |
| Contact spacing | > 3 mm |
| Height | 71 mm |
| Width | 71 mm |

Materials

| | |
|--------------------|------|
| Surface appearance | matt |
|--------------------|------|

Installation, mounting

| | |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

Connection

| | |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60669-1 |
| Connection terminals | according to VDE 0632-1 |

Equipment

| | |
|----------------|----|
| Heating switch | No |
|----------------|----|

Use cases

| | |
|-------------|---------------|
| Application | Light control |
|-------------|---------------|

| | |
|-----------------------|--|
| Safety | |
| Protection index IP | IP20 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |
| Impact strength | IK07 |
| Identification | |
| Application, usage | Light control |
| Main design line | Light control |
| Instructions | |
| Information text | spreader claws, insulated to the supporting ring, self-resetting |