



3315402089

**VGA soc. out., R.1/R.3, p. white glossy**

**Technical properties**

**Connectivity**

Outlet	with straight outlet
Plug type	S-VGA compatible
Connectors / jacks	with 15pole D-subminiature jack (front)

**Dimensions**

Insertion depth	12 mm
-----------------	-------

**Frequency**

Frequency range video	max. 160 MHz
-----------------------	--------------

**Screen**

Resolution	max. 1280 x 1024 px
------------	---------------------

**Materials**

Colour of labelling	105,105,105
Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material for printing	ASA polar white
Surface appearance	glossy

**Installation, mounting**

Installation mode	without spreader claws ; for screw fastening
-------------------	--

**Connection**

Type of connection	with backside jack for connecting to pre-assembled VGA cable
Connection	with 15pole D-subminiature double jack

**Settings**

Shading parameter	R1_biały
Laser parameter	R1_weiß

**Equipment**

Type of configuration	Laserdruck
Supporting plate / Supporting ring	with supporting ring

**Safety**

REACH conform	Yes
RoHS conform	Yes

**Identification**

Application, usage

Communication technology

Main design line

Berker R.1/R.3/R.8

Secondary design line(s)

Berker R.1 ; Berker R.3 ; Berker R.8

---

**Instructions**

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74