



41091404

**SCHUKO soc.out. LEDorient.,enhncd contact prot.,screw-in lift term.,B.7,al.lacq.**

#### Technical properties

##### Architecture

Design according to DIN 49440

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 16 A

##### Electric current

Rated current 16 A

##### Dimensions

Insertion depth 32 mm

##### Power

Power consumption 0.25 W/0.35 VA

##### Cover, door

Cover Central cover plate

##### Detection

Sensor integrated brightness sensor that switches the orientation light on at twilight and off when there is sufficient brightness

##### Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance matt

##### Lighting control

Switch-off brightness  $\approx$  4 lx

Switch-on brightness  $\approx$  2 lx

Light intensity (white) 0.2 cd

##### LED control

LED white LED light ; long service life of the LED

##### Installation, mounting

Installation mode with spreader claws

---

**Connection**

Conductor cross-section (rigid)	max. 2.5 mm <sup>2</sup>
Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

---

**Cable**

Wiring	through-wiring possible, therefore also ideal for retrofitting
--------	--

---

**Equipment**

Lighting	additional benefit by combination of a socket outlet with an orientation light
----------	--

---

**Use**

Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals

---

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

---

**Identification**

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7

---

**Instructions**

Information text	Caution! Items with special flush-mounted insert. Centre plates with LED orientation lights are not compatible with the standard socket outlets.
------------------	--