



3315416084

VGA socket outlet with screw-in lift terminals, Q.x, alu velvety, lacquered

Technical properties

Connectivity

| | |
|--------------------|-----------------------------------------|
| Outlet | with straight outlet |
| Plug type | S-VGA compatible |
| Connectors / jacks | with 15pole D-subminiature jack (front) |

Frequency

| | |
|-----------------------|--------------|
| Frequency range video | max. 160 MHz |
|-----------------------|--------------|

Screen

| | |
|------------|---------------------|
| Resolution | max. 1280 x 1024 px |
|------------|---------------------|

Materials

| | |
|-----------------------|-----------|
| Colour of design line | aluminium |
| Surface appearance | velvety |

Installation, mounting

| | |
|-------------------|------------------------|
| Installation mode | without spreader claws |
|-------------------|------------------------|

Connection

| | |
|-------------------------|------------------------------------------------------------------|
| Conductor cross-section | max. 1.5 mm ² |
| Type of connection | with screw-in lift terminals for connection to 15-core VGA cable |

Equipment

| | |
|------------------------------------|----------------------|
| Supporting plate / Supporting ring | with supporting ring |
|------------------------------------|----------------------|

Use

| | |
|------------------------------------------|------------------------------|
| Differentiation characteristic 3 - Sales | with screw-in lift terminals |
|------------------------------------------|------------------------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |

Identification

| | |
|--------------------------|---------------------------------------------------|
| Main design line | Berker Q.1/Q.3/Q.7/Q.9 |
| Secondary design line(s) | Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9 |

Instructions

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74