



41097006

SCHUKO soc.out. LEDorient.,enhncd contact prot.,screw-in lift term.,K1,ant.,lacq

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Power

Power consumption	0.25 W/0.35 VA
-------------------	----------------

Cover, door

Cover	Central cover plate
-------	---------------------

Detection

Sensor	integrated brightness sensor that switches the orientation light on at twilight and off when there is sufficient brightness
--------	-----------------------------------------------------------------------------------------------------------------------------

Materials

Colour of design line	anthracite
Colour	anthracite
Material / workmanship	lacquered
Surface appearance	mat

Lighting control

Switch-off brightness	≈ 4 lx
Switch-on brightness	≈ 2 lx
Light intensity (white)	0.2 cd

LED control

LED	white LED light ; long service life of the LED
Installation, mounting	
Installation mode	with spreader claws
Connection	
Conductor cross-section (rigid)	max. 2.5 mm ²
Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Cable	
Wiring	through-wiring possible, therefore also ideal for retrofitting
Use	
Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals
Safety	
IK protection code against mechanical impacts	05
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes
Identification	
Main design line	Berker K.1
Instructions	
Information text	Caution! Items with special flush-mounted insert. Centre plates with LED orientation lights are not compatible with the standard socket outlets.