



41092045

SCHUKO soc.out. LEDorient.,enhncd contact prot.,screw-in lift term.,R.cl,bl.

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Power

Power consumption	0.25 W/0.35 VA
-------------------	----------------

Cover, door

Cover	Central cover plate
-------	---------------------

Detection

Sensor	integrated brightness sensor that switches the orientation light on at twilight and off when there is sufficient brightness
--------	---

Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black

Lighting control

Switch-off brightness	≈ 4 lx
Switch-on brightness	≈ 2 lx

Light intensity (white)

0.2 cd

LED control

LED	white LED light, long service life of the LED
-----	---

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Conductor cross-section (rigid)	2.5
Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

Cable

Wiring	through-wiring possible, therefore also ideal for retrofitting
--------	--

Settings

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

Equipment

Type of configuration	Laserdruck
Lighting	additional benefit by combination of a socket outlet with an orientation light

Use

Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Main design line	Serie R.classic
------------------	-----------------

Instructions

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
-------------------	--

Information text	Caution! Items with special flush-mounted insert. Centre plates with LED orientation lights are not compatible with the standard socket outlets.
------------------	--