



41102007

SCHUKO soc.out. LED+"ZSV" impr.,enhncd contact prot.,screw-in lift ,R.1.3,or.

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Design lines special colours	orange
Colour	orange
Colour	orange
RAL colour	RAL 2003 - Pastel orange
Material	thermoplastic
Surface appearance	glossy

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

Use

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals

Safety

Protection index IP	IP20
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8

Instructions

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--
