



4522

Technical properties

Functions

Function Suitable for HDTV

Connectivity

Connectors / jacks remote supply via F-socket

Reception / transmission for terrestrial reception, for digital and analogue transmission

Voltage

Voltage DC voltage conducting

Frequency

Broadband technology 5...2400 MHz

Resistance

Wave impedance 75 Ω

Attenuation

Tap loss at 2150 MHz 2.5 dB

Tap loss at 860 MHz 4 dB

- at 113 ... 174 MHz 3.5 dB

- at 174 ... 862 MHz 4 dB

- at 4 ... 30 MHz 3.5 dB

- at 40 ... 68 MHz 3.5 dB

- at 87.5 ... 108 MHz 3.8 dB

- at 950 ... 2400 MHz 1.5...3 dB

Materials

Material metal

Installation, mounting

System for community, DVB-T and broadband cable systems, for single and distributor SAT systems

Connection

Type of connection with screw terminals

Cable

For coaxial cables 75 Ω

Use

Differentiation characteristic 3 - Sales DC-permeable

Standards

General standards

IEC 169-2 and EN 50083-2, EN 60728-4, -11

Safety

Shielding value

according to EMC protection class A

Identification

Application, usage

Communication technology

Main design line

Communication technology