



41102045

**SCHUKO soc.out. control LED,enhncd contact prot.,screw-in lift term.,R.1.3,bl.**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
-----------------	-------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black
Surface appearance	glossy

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

**Settings**

Shading parameter	R1_czarny
-------------------	-----------

**Equipment**

---

Type of configuration	Laserdruck
-----------------------	------------

**Use**

---

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals

**Safety**

---

Protection index IP	IP20
Protection	Enhanced contact protection
With enhanced contact protection	Yes

**Identification**

---

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8

**Instructions**

---

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--