



41106086

SCHUKO soc.out. LED,labfield,enhncd contact prot.,screw-in lift ,Q.x,ant.velv

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	duroplastic
Surface appearance	velvety

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Differentiation characteristic 2 - Sales

enhanced contact protection

Differentiation characteristic 3 - Sales

Screw-in lift terminals

Safety

IK protection code against mechanical impacts

05

Protection index IP

IP20

Protection

Enhanced contact protection

With enhanced contact protection

Yes

Identification

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

Instructions

Information text

Labelling field height arranged for P-touch strips 6 mm.