



47516074

**SCHUKO sock. outl. w. hing. cov. a. enh. cont. prot., Q.x, alu velvety, lacq.**

#### Technical properties

##### Architecture

|             |                        |
|-------------|------------------------|
| Design      | according to DIN 49440 |
| Fixing mode | flush-mounting         |

##### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

##### Main electrical features

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Frequency       | 50/60 Hz |
| Rated current   | 16 A     |

##### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

##### Cover, door

|               |                                   |
|---------------|-----------------------------------|
| Hinged covers | with hinged cover that falls back |
| Cover         | Central cover plate               |

##### Materials

|                    |                            |
|--------------------|----------------------------|
| Colour             | aluminium                  |
| Colour             | aluminium optics           |
| RAL colour         | RAL 9006 - White aluminium |
| Material           | thermoplastic              |
| Surface appearance | velvety                    |
| Metallic colour    | Yes                        |

##### Installation, mounting

|                   |                     |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

##### Connection

|                      |                          |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1  |
| Type of connection   | with plug-in terminals   |

##### Use

|  |                             |
|--|-----------------------------|
| Differentiation characteristic 2 - Sales | enhanced contact protection |
|--|-----------------------------|

##### Safety

|   |  |
|---|--|
| IK protection code against mechanical impacts | 02                                     |
| Protection index IP                           | IP20                                   |
| REACH conform                                 | Yes                                    |
| RoHS conform                                  | Yes                                    |
| Halogen free                                  | No                                     |
| Protection                                    | enhanced contact protection VDE 0620-1 |
| With enhanced contact protection              | Yes                                    |

#### Identification

|                          |  |
|--------------------------|--|
| Main design line         | Berker Q.1/Q.3/Q.7/Q.9                         |
| Secondary design line(s) | Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9 |