



503501

## Series push-button NC contact and NO contacts with isolated input terminals

### Technical properties

#### Architecture

Type of control unit double rocker

#### Functions

Switching angle 3.5 °

#### Configuration

Switch mode 1 NO, 1 NC, separate input terminals

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Momentary-contact current 10 A

#### Dimensions

Depth 41.6 mm

Insertion depth 31.3 mm

Height 71 mm

Width 71 mm

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

#### Equipment

Lighting can be illuminated using neon lamp, incandescent or LED unit with N terminal ; for lighting and monitoring circuit

#### Use cases

Application Light control

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

---

**Identification**

---

Application, usage	Light control
Main design line	Light control

---

**Instructions**

---

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--

---