



5036

Push-button change-over contact illuminated

Technical properties

Architecture

Type of control unit rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode change-over contact, usable as NC or NO

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 42 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode with spreader claws

Connection

Conductor cross-section (rigid) max. 2.5 mm²

Type of connection with plug-in terminals

Equipment

Quantity of NC contacts 1

Quantity of NO contacts 1

Lighting for lighting and monitoring circuit

Use cases

Application Barrier-free application ; HVAC-control ; Light control

Safety

REACH conform Yes

RoHS conform	Yes
Halogen free	Yes

Identification

Main design line	Light control
------------------	---------------

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--