




75142155

IP20



Touch sensor, 2-gang comf, intg bus coupling unit, KNX - R.3, glass black

## Technical properties

### Functions

With room temperature controller	Yes
----------------------------------	-----

Function

for switch, push-button, dimmer and shutter functions ; Blocking function for sensor surface e.g. for cleaning the glass surface

### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--------------------------------------------

### Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	0
-------------------	---

Operation

operation by gently touching the sensor surfaces on the white LED

### Dimensions

Depth	23 mm
-------	-------

Height	152 mm
--------	--------

Width	81 mm
-------	-------

### Power

Current consumption	12.5 mA
---------------------	---------

### Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	-----------------------------------------------------------------------------------------

### Screen

With display	No
--------------	----

### Materials

Colour of labelling	217,217,217
---------------------	-------------

Colour of design line	glass black
-----------------------	-------------

Surface appearance	glossy
--------------------	--------

### LED control

LED	with blue operation LED and 4 white status LEDs
-----	-------------------------------------------------

### Installation, mounting

Installation mode	for vertical mounting
-------------------	-----------------------

### Connection

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

Bus connection	bus connection via connecting terminal
----------------	----------------------------------------

### Scope of delivery

Bus connection included	Yes
-------------------------	-----

### Accessories included

Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform R.1/R.3 ; for suitable frames in the same "style" for additional applications, see the Design line R.x
-------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

### Equipment

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Type of configuration	Laserdruck

### Use

Differentiation characteristic 3 - Sales	with integral bus coupling unit
------------------------------------------	---------------------------------

### Safety

REACH conform	Yes
RoHS conform	Yes

### Use conditions

Operating temperature	-5...45 °C
Temperature	temperature measurement via internal temperature sensor or external communication object ; integrated temperature sensor for operation as controller extension unit ; additional connection for external temperature sensor

### Identification

Application, usage	KNX - operating systems
Main design line	KNX - Berker R.3 - configured
Secondary design line(s)	KNX ; Berker R.3