




75142165

IP20



Touch sensor, 2-gang comf, intg bus coupling unit, KNX - R.1, glass black

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	Yes
----------------------------------	-----

Function	for switch, push-button, dimmer and shutter functions, Blocking function for sensor surface e.g. for cleaning the glass surface
----------	---

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	0
-------------------	---

Operation	operation by gently touching the sensor surfaces on the white LED
-----------	---

Dimensions

Depth	23 mm
-------	-------

Height	152 mm
--------	--------

Width	81 mm
-------	-------

Power

Current consumption	12.5 mA
---------------------	---------

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	Yes
--------------	-----

Materials

Colour of labelling	217,217,217
---------------------	-------------

Colour of design line	glass black
-----------------------	-------------

Colour	black
--------	-------

RAL colour	RAL 9005 - Jet black
------------	----------------------

Material	glass
----------	-------

Type of surface treatment	Painted
---------------------------	---------

LED control

LED	with blue operation LED and 4 white status LEDs
-----	---

Installation, mounting	
Installation mode	for vertical mounting
Connection	
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Scope of delivery	
Bus connection included	Yes
Accessories included	
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform R.1/R.3, for suitable frames in the same "style" for additional applications, see the Design line R.x
Equipment	
Number of actuation points	4
With anti-theft/dismantling protection	Yes
Type of configuration	Laserdruck
Use	
Differentiation characteristic 3 - Sales	with integral bus coupling unit
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-5...45 °C
Temperature	temperature measurement via internal temperature sensor or external communication object, integrated temperature sensor for operation as controller extension unit, additional connection for external temperature sensor
Identification	
Application, usage	KNX - operating systems
Main design line	KNX - Berker R.1 - configured
Secondary design line(s)	KNX, Berker R.1