



75144155

IP20



Touch sensor, 4-gang comf, intg bus coupling unit, KNX - R.3, glass black

Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller Yes

Function for switch, push-button, dimmer and shutter functions ; Blocking function for sensor surface e.g. for cleaning the glass surface

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 0

Operation operation by gently touching the sensor surfaces on the white LED

Dimensions

Depth 23 mm

Height 152 mm

Width 81 mm

Power

Current consumption 12.5 mA

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of labelling 217,217,217

Colour of design line glass black

Colour black

RAL colour RAL 9005 - Jet black

Material glass

Surface appearance glossy

Type of surface treatment Tampography

LED control

Installation, mounting

Installation mode	for vertical mounting
-------------------	-----------------------

Connection

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

Bus connection	bus connection via connecting terminal
----------------	--

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Accessories included

Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform R.1/R.3 ; for suitable frames in the same "style" for additional applications, see the Design line R.x
-------------------	---

Equipment

Number of actuation points	8
----------------------------	---

With anti-theft/dismantling protection	Yes
--	-----

Type of configuration	Laserdruck
-----------------------	------------

Use

Differentiation characteristic 3 - Sales	with integral bus coupling unit
--	---------------------------------

Safety

Protection index IP	IP20
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Temperature	temperature measurement via internal temperature sensor or external communication object ; integrated temperature sensor for operation as controller extension unit ; additional connection for external temperature sensor
-------------	---

Identification

Application, usage	KNX - operating systems
--------------------	-------------------------

Main design line	KNX - Berker R.3 - configured
------------------	-------------------------------

Secondary design line(s)	KNX ; Berker R.3
--------------------------	------------------