



41527103

**SCHUKO soc.out. overvoltage prot., lab. field, screw term., K.5, al. matt lacq.**

**Technical properties**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Controls and indicators**

Message with acoustic fault signal

**Main electrical features**

Nominal voltage 250 V  
 Rated voltage 250 V AC  
 Frequency 50/60 Hz  
 Rated current 16 A

**Voltage**

Overvoltage protection according to EN 61643 and VDE 0675-6-11

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line aluminium  
 Material / workmanship lacquered  
 Surface appearance matt

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1  
 Connection terminals according to VDE 0620-1  
 Type of connection with screw terminals

**Equipment**

Lighting with indicator LED for On/Error

**Use cases**

---

Application

Security and safety systems

**Use**

---

Differentiation characteristic 1 - Sales

with labelling field

Differentiation characteristic 3 - Sales

Screw terminals

**Safety**

---

Protection

without enhanced contact protection

With enhanced contact protection

No

**Identification**

---

Main design line

Berker K.5

**Instructions**

---

Information text

Labelling field height arranged for P-touch strips 6 mm.