



41527103

SCHUKO soc.out. overvoltage prot., lab. field, screw term., K.5, al. matt lacq.

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Controls and indicators

Message	with acoustic fault signal
---------	----------------------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Voltage

Overvoltage protection	according to EN 61643 and VDE 0675-6-11
------------------------	---

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	aluminium
Colour	aluminium
Material / workmanship	lacquered
Surface appearance	matt

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1

Use cases

Use

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	Screw terminals

Safety

Protection index IP	IP20
Protection	without enhanced contact protection
With enhanced contact protection	No

Identification

Main design line	Berker K.5
------------------	------------

Instructions

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--