



47087009

SCHUKO soc.out. residual current circuit-breaker,enhncd contact prot.,K.1,wh.gl.

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting
Type	type A for alternating currents and pulsating direct currents

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Measurement error current	30 mA
Rated current	16 A
Surge current resistance	250 A (8/20) μ s
Short-circuit resistance (with back-up fuse 20 AgL)	3 kA

Dimensions

Insertion depth	31.9 mm
-----------------	---------

Tripping

Trigger time	\leq 30 ms
--------------	--------------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use cases

Application	Security and safety systems
-------------	-----------------------------

Use

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

Standards

Tested	conform VDE 0664 (EN 61008)
--------	-----------------------------

Safety

IK protection code against mechanical impacts	07
---	----

Protection index IP	IP20
---------------------	------

Protection	Enhanced contact protection
------------	-----------------------------

With enhanced contact protection	Yes
----------------------------------	-----

Identification

Main design line	Berker K.1
------------------	------------