



75163370



IP20



## Technical properties

### Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

### Controls and indicators

With LED indication	Yes
Number of buttons	3

### Dimensions

Labelling field length (W x H)	66.8 x 15.7 mm
Height	55.1 mm
Width	70.5 mm

### Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

### Screen

With display	No
--------------	----

### Materials

Colour of labelling	105,105,105
Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material for printing	Paper
Surface appearance	glossy
Type of surface treatment	untreated
Material family	Plastic

### LED control

LED - KNX	with white operation LED and 6 red status LEDs
-----------	--

### Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

### Scope of delivery

Bus connection included	No
-------------------------	----

### Equipment

Number of actuation points	6
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 3gang
<b>Use</b>	
Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with horizontal operation
<b>Safety</b>	
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
<b>Identification</b>	
Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	Berker K.1 ; KNX