



47432089

SCHUKO soc. out., R.1/R.3, p. white glossy

Technical properties

Architecture

| | |
|-------------|------------------------|
| Design | according to DIN 49440 |
| Fixing mode | flush-mounting |

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |
| Frequency | 50/60 Hz |
| Rated current | 16 A |

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Dimensions

| | |
|---|-------|
| Insertion depth | 32 mm |
| Installation depth, flush-mounted boxes | 31 mm |

Cover, door

| | |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

Materials

| | |
|-----------------------|-----------------------|
| Colour of design line | polar white |
| Colour | polarwhite |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | thermoplastic |
| Material for printing | ASA polar white |
| Metallic colour | No |

Installation, mounting

| | |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

Connection

| | |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1 |
| Type of connection | with plug-in terminals |

Settings

| | |
|----------------------------------|-------------------------------------|
| Shading parameter | R1_biały |
| Laser parameter | R1_weiß |
| Equipment | |
| Type of configuration | Laserdruck |
| Safety | |
| Protection index IP | IP20 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |
| Protection | without enhanced contact protection |
| With enhanced contact protection | No |
| Identification | |
| Main design line | Berker R.1/R.3/R.8 |
| Secondary design line(s) | Berker R.1, Berker R.3, Berker R.8 |